

## **Important**

- The interior tube cross-sections in front of the HoseGuard® must be larger than or equal to the interior diameter of the HoseGuard®. (The HoseGuard® nominal widths are for 1/4" = 6 mm, 3/8" = 10 mm, 1/2" = 12 mm, 3/4" = 19 mm, 1" = 25 mm).
- The following figures must be observed as the minimum interior hose diameter: 1/4" = 6 mm, 3/8" = 10 mm, 1/2" = 13 mm, 3/4" = 16 mm / 1" = 19 mm.
- Extremely long hoses may cause a high pressure drop at the end of the hose. This must be accounted for during planning. Please consider that we need sufficient flow to enable the HoseGuard® to close!



Closing point tables HoseGuard® 1/4" 3/8" 1/2" 3/4" 1"



